

Goodyear Gauntlet[®] Washdown Hose

Turn to Applied Industrial Technologies to keep you InSync[®] with superior hose performance in high-pressure washdown applications. The Goodyear Gauntlet is durably designed for a long service life and helps the Bakery Industry achieve maximum cleanability and decreased bacterial growth. Goodyear Hose is stocked at an Applied service center near you.

Bakery Industry Applications:

- High pressure cleaning and washdown

Features/Benefits:

- **Highly visible, exclusive yellow Carbryn[®] cover** is impervious to industrial oils and therefore resists degradation
- **Gauntlet 1500 textile reinforcement** will not rust or decompose and is resistant to runover by heavy machinery
- **3/8 and 1/2 inch sizes are cut, coupled and wrapped in 50, 75 and 100-foot lengths for convenience** and are equipped with 3/8 x 3/8 male x male swivel fittings
- **Two strengths for working pressures up to 1500 and 3000 psi** cover a variety of application standards



APPLIED
Industrial Technologies[®]

Value Through Innovation

Applied Industrial Technologies and Goodyear InSync® with the concerns of the Bakery Industry

Goodyear Gauntlet 1500

Application:

- For pressure washer equipment with working pressures up to 1500 psi

Construction:

- Tube: Black Chemigum®
- Reinforcement: Braided high strength yarn
- Cover: Yellow oil-resistant Carbryn® RMA Class A (high oil resistance)

Temperature:

- -20°F to 200°F (-29°C to 93.3°C)

Packaging:

- Cut, coupled and wrapped in 50, 75 or 100-foot lengths with 3/8 x 3/8 male x male swivel fittings. Also available in reel form.

Nom. ID		Nom. OD		Max. WP		Weight	
in.	mm.	in.	mm.	psi	Mpa	lb./ft.	kg./m.
3/8	9.5	.750	19.1	1500	10.4	.18	.27
1/2	12.7	.840	21.0	1200	8.3	.19	.29



Goodyear Gauntlet 3000

Application:

- For pressure washer equipment with working pressures up to 3000 psi

Construction:

- Tube: Black Chemigum
- Reinforcement: One wire braid
- Cover: Yellow oil-resistant Carbryn RMA Class A (high oil resistance)

Temperature:

- -20°F to 250°F (-29°C to 121°C)


Packaging:

- Cut, coupled and wrapped in 50, 75 or 100-foot lengths with 3/8 x 3/8 male x male swivel fittings. Also available in reel form.

Nom. ID		Nom. OD		Max. WP		Weight	
in.	mm.	in.	mm.	psi	Mpa	lb./ft.	kg./m.
3/8	9.5	.692	17.6	3000	20.6	.22	.33
1/2	12.7	.820	20.0	3000	20.6	.30	.45



Contact Your Local Authorized Service Center
at **(877) 279-2799**



APPLIED
Industrial Technologies®

Value Through Innovation

One Applied Plaza
Cleveland, Ohio 44115-5000
Toll Free Phone: 1-877-279-2799
<http://www.appliedindustrial.com>