

Prevent Dust and Spillage

Applied Industrial Technologies and Nelson Williams Linings, Inc.



MINING INDUSTRY

The EZ-SKIRT® Skirting System is a world-class sealing system that is reducing cleanup and maintenance costs at installations worldwide.

The simple and effective two-part conveyor skirting system, from Nelson Williams, prevents dust and spillage. Adjustment can be made by just one person, minimizing man-hours. EZ-SKIRT is uniquely designed without nuts, bolts, clamps or fasteners, making the system virtually maintenance free.

Applications

- Hoppers
- Chutes
- Conveyors



*Applied Industrial Technologies.
Keeping customer safety and
productivity in mind.*

Features and Benefits

• Simple Two-Part System

Mount the 5-foot stainless steel hangers to the chute wall, insert the skirting "T" lugs into the serrated channels, and adjust the skirting to the belt. Adjusts in seconds by pushing down or tapping with a mallet. No nuts, bolts, clamps or fasteners. Quick, easy peel-away removal for maintenance. Sealing strips come in 5-foot lengths with overlapping joints for a tight seal.

• Easy Installation

Can easily be retrofit to your existing chute walls. The skirting is available in many sizes, thickness and compounds. Hangers are available in 45, 60, 70, 80 and 90-degree angles for a custom fit to any trough angle to seal your conveyor like no other system.

• Proven Performance

The sealing strip is high quality press-molded rubber that substantially outlasts conventional skirting. From severe duty hard-rock installations to self-adjusting rubber that contours and flexes with the belt to prevent dust leakage, EZ-SKIRT provides simple and effective sealing.

A product of:



Authorized distributor:



EZ-SKIRT® Skirting System is SIMPLE, QUICK and EFFECTIVE.



The EZ-SKIRT® Skirting System was developed in the tough hard-rock mining conditions of the Minnesota Iron Range. Plant managers and maintenance personnel alike are finding that the EZ-SKIRT® Skirting System provides the quickest return on investment for their conveyor system.



Stitch weld hanger to hopper
(45° shown)



Easy peel-away removal



Serrated channels hold skirting securely
– skirting will not creep back up

Part No.	Description
12-NAT-60-26-TAIL	1/2"X26"X56"NAT 60 DURO TAILSKIRT
34-NAT-40-06-L	3/4"X6"NAT RUBB 40 DURO LH EZ-SKIRT
34-NAT-40-06-R	3/4"X6"NAT RUBB 40 DURO RH EZ-SKIRT
34-NAT-40-07-L	3/4"X7"NAT RUBB 40 DURO LH EZ-SKIRT
34-NAT-40-07-R	3/4"X7"NAT RUBB 40 DURO RH EZ-SKIRT
34-NAT-40-08-L	3/4"X8"NAT RUBB 40 DURO LH EZ-SKIRT
34-NAT-40-08-R	3/4"X8"NAT RUBB 40 DURO RH EZ-SKIRT
34-NAT-40-09-L	3/4"X9"NAT RUBB 40 DURO LH EZ-SKIRT
34-NAT-40-09-R	3/4"X9"NAT RUBB 40 DURO RH EZ-SKIRT
34-NAT-40-26-TAIL	3/4"X26"X56"NAT 40 DURO TAILSKIRT
34-NAT-60-06-L	3/4"X6"NAT RUBB 60 DURO LH EZ-SKIRT
34-NAT-60-06-R	3/4"X6"NAT RUBB 60 DURO RH EZ-SKIRT
34-NAT-60-07-L	3/4" X7"NAT RUBB 60DURO LH EZ-SKIRT
34-NAT-60-07-R	3/4"X7"NAT RUBB 60 DURO RH EZ-SKIRT
34-NAT-60-08-L	3/4"X8"NAT RUBB 60 DURO LH EZ-SKIRT
34-NAT-60-08-R	3/4"X8"NAT RUBB 60 DURO RH EZ-SKIRT
34-NAT-60-09-L	3/4"X9"NAT RUBB 60 DURO LH EZ-SKIRT
34-NAT-60-09-R	3/4"X9"NAT RUBB 60 DURO RH EZ-SKIRT
34-NAT-60-26-TAIL	3/4"X26"X56"NAT 60 DURO TAILSKIRT
5-SS-2-45	5FT 2"FACE, 45 DEG EZ-SKIRT HANGER
5-SS-2-60	5FT 2"FACE, 60 DEG EZ-SKIRT HANGER
5-SS-2-70	5FT 2"FACE, 70 DEG EZ-SKIRT HANGER
5-SS-2-80	5FT 2"FACE, 80 DEG EZ-SKIRT HANGER
5-SS-2-90	5FT 2"FACE, 90 DEG EZ-SKIRT HANGER
5-SS-4-45	5FT 4"FACE, 45 DEG EZ-SKIRT HANGER
5-SS-4-60	5FT 4"FACE, 60 DEG EZ-SKIRT HANGER
5-SS-4-70	5FT 4"FACE, 70 DEG EZ-SKIRT HANGER
5-SS-4-80	5FT 4"FACE, 80 DEG EZ-SKIRT HANGER
5-SS-4-90	5FT 4"FACE, 90 DEG EZ-SKIRT HANGER
12-NAT-60-09-R	1/2"X9"NAT RUBB 60 DURO RH EZ-SKIRT

Part No.	Description
12-NAT-60-26-TAIL	1/2"X26"X56"NAT 60 DURO TAILSKIRT
34-NAT-40-06-L	3/4"X6"NAT RUBB 40 DURO LH EZ-SKIRT
34-NAT-40-06-R	3/4"X6"NAT RUBB 40 DURO RH EZ-SKIRT
34-NAT-40-07-L	3/4"X7"NAT RUBB 40 DURO LH EZ-SKIRT
34-NAT-40-07-R	3/4"X7"NAT RUBB 40 DURO RH EZ-SKIRT
34-NAT-40-08-L	3/4"X8"NAT RUBB 40 DURO LH EZ-SKIRT
34-NAT-40-08-R	3/4"X8"NAT RUBB 40 DURO RH EZ-SKIRT
34-NAT-40-09-L	3/4"X9"NAT RUBB 40 DURO LH EZ-SKIRT
34-NAT-40-09-R	3/4"X9"NAT RUBB 40 DURO RH EZ-SKIRT
34-NAT-40-26-TAIL	3/4"X26"X56"NAT 40 DURO TAILSKIRT
34-NAT-60-06-L	3/4"X6"NAT RUBB 60 DURO LH EZ-SKIRT
34-NAT-60-06-R	3/4"X6"NAT RUBB 60 DURO RH EZ-SKIRT
34-NAT-60-07-L	3/4" X7"NAT RUBB 60DURO LH EZ-SKIRT
34-NAT-60-07-R	3/4"X7"NAT RUBB 60 DURO RH EZ-SKIRT
34-NAT-60-08-L	3/4"X8"NAT RUBB 60 DURO LH EZ-SKIRT
34-NAT-60-08-R	3/4"X8"NAT RUBB 60 DURO RH EZ-SKIRT
34-NAT-60-09-L	3/4"X9"NAT RUBB 60 DURO LH EZ-SKIRT
34-NAT-60-09-R	3/4"X9"NAT RUBB 60 DURO RH EZ-SKIRT
34-NAT-60-26-TAIL	3/4"X26"X56"NAT 60 DURO TAILSKIRT
5-SS-2-45	5FT 2"FACE, 45 DEG EZ-SKIRT HANGER
5-SS-2-60	5FT 2"FACE, 60 DEG EZ-SKIRT HANGER
5-SS-2-70	5FT 2"FACE, 70 DEG EZ-SKIRT HANGER
5-SS-2-80	5FT 2"FACE, 80 DEG EZ-SKIRT HANGER
5-SS-2-90	5FT 2"FACE, 90 DEG EZ-SKIRT HANGER
5-SS-4-45	5FT 4"FACE, 45 DEG EZ-SKIRT HANGER
5-SS-4-60	5FT 4"FACE, 60 DEG EZ-SKIRT HANGER
5-SS-4-70	5FT 4"FACE, 70 DEG EZ-SKIRT HANGER
5-SS-4-80	5FT 4"FACE, 80 DEG EZ-SKIRT HANGER
5-SS-4-90	5FT 4"FACE, 90 DEG EZ-SKIRT HANGER

GSA Contract Holder
Contract GS-06F-0042R

Contact Your Local Applied® Service Center
1-877-279-2799

Authorized distributor:

APPLIED
Industrial Technologies®

Corporate Headquarters
1 Applied Plaza
Cleveland, Ohio 44115
Toll Free Phone: 1-877-279-2799
Applied.com

WARNING: Injury, death, property damage, and/or equipment failure may result from the misuse or misapplication of the products featured in this publication. The information in this publication is provided "AS IS," WITHOUT ANY WARRANTY OF THE INFORMATION'S ACCURACY OR THE PRODUCTS' SUITABILITY FOR ANY PARTICULAR USE.