



Applied Industrial Technologies - Your Fluid Power Connection

Pneumatic Packaging Solutions

Applications in bottling, canning, boxing, labeling, and other packaging areas place extremely high demands on pneumatic components. **They must withstand repetitive operations at high speeds for extended periods of time.** It is also essential that they are easy to maintain, and small enough to maximize space on the assembly line.

Typical pneumatic components meet some of these needs but usually not all. **APPLIED** offers ARO components to meet them all. Call your local Applied representative for these and other pneumatic packaging solutions.

ARO Module / Air 1000 Piggyback Filter / Regulator


- **Feature:**
Combined filter / regulator
- **Benefit:**
Saves valuable space and adds flexibility

ARO Sierra Valves

- **Feature:**
Only 15 mm wide, with 0.25 Cv flow
- **Benefit:**
Performs powerful motion control functions utilizing minimal space.

New ARO Select Series Cylinders

- **Feature:**
Does not build up heat due to the barrel ID chemistry, surface finish and part tolerances.
- **Benefit:**
Smoother operation and longer seal life than stainless steel barreled cylinders





ARO STAINLESS FRL PARTS

Part Numbers		Specifications						Pricing	
		Product Name	Port Size (NPT)	Flow Size (SCFM)	Bowl Capacity	Pressure Range	Weight (lbs.)	List Price	Your Price
FP0721658	P29112-600	Module/Air 1000	1/8	13	0.6 oz	5-125	2.050	\$41.62	\$35.27
FP0625044	P29122-600	Module/Air 1000	1/4	13	0.6 oz	5-125	2.030	\$41.62	\$35.27



ARO SIERRA VALVES

Part Numbers		Specifications					Pricing		
		Description	Port Size (BSP)	CV Flow	Voltage	Actuator/Return	Weight (lbs.)	List Price	Your Price
FP0547826	S5SSMC	Single Solenoid, 2 Position	M5	0.250	120 Vac	Solenoid/Spring	1.500	\$66.58	\$56.20
FP0547827	S5SSMD	Single Solenoid, 2 Position	M5	0.250	24 VDC	Solenoid/Spring	1.500	\$66.58	\$56.20
FP0547806	S5DSMC	Double Solenoid, 2 Position	M5	0.250	120 Vac	Solenoid/Solenoid	1.700	\$99.04	\$83.60
FP0547807	S5DSMD	Double Solenoid, 2 Position	M5	0.250	24 VDC	Solenoid/Solenoid	1.700	\$99.04	\$83.60



NEW SELECT SERIES CYLINDERS

Part Numbers		Specifications			Pricing	
		Description	Bore (in.)	Mounting Style	List Price	Your Price
FP1197277	SLD04-CBP-010	Double Acting	7/16	Pivot	\$22.87	\$19.45
FP1197278	SLD04-CBP-014	Double Acting	7/16	Pivot	\$24.47	\$20.80
FP1197279	SLD04-CBP-020	Double Acting	7/16	Pivot	\$24.47	\$20.80

Find these and other quality fluid power components in our Fluid Power Connection catalog all at great prices and backed by great customer service. Call your local Applied Service Center at 1-877-279-2799 to order your **FREE** catalog today. Or, visit us on the web at www.fluidpowerconnection.com for online ordering convenience.



Contact Your Local Authorized Service Center
1-877-279-2799

WARNING: Injury, death, property damage, and/or equipment failure may result from misuse or misapplication of the products featured in this publication. The information in this publication is provided "AS IS," WITHOUT WARRANTY OF THE INFORMATION'S ACCURACY OR THE PRODUCTS' SUITABILITY FOR ANY PARTICULAR USE.

APPLIED
Industrial Technologies®

Value Through Innovation

One Applied Plaza
Cleveland, Ohio 44115-5000
Toll Free Phone: 1-877-279-2799
www.appliedindustrial.com