

New Lubrication Technology Increases Your Uptime



Staying InSync With Technology.

**Use at any location
requiring precise
timely lubrication
or at hard to reach
lubrication points**

Typical Applications:

Conveyors

Pumps

Fans

Crushers

Screens

Bucket Elevators

Remove the task of lubricating equipment from your to-do list. The **PERMA® PRO Lubrication System** delivers precise lubrication where and when you need it. It's just one more solution that **Applied Industrial Technologies** offers to reduce downtime, extend equipment life and maximize your plant's operation.

► Features and Benefits:

- ❑ **Two styles accommodate any area of your operation –**
PERMA PRO is battery operated and PERMA PRO C is directly wired to existing PLC
- ❑ **Variable Discharge Settings –**
One day to 24 months
- ❑ **Two Sizes –**
250cc and 500cc
- ❑ **No Guesswork –**
Visible piston and LED display reveal information concerning discharge settings and remaining lubricant
- ❑ **-4° F to 140° F Temperature Range –**
Can be used inside or outside

Combine the PERMA PRO with a PERMA MP6 for multiple point lubrication:

- ❑ Offers two to six individual outlets
- ❑ No pressure loss at individual ports
- ❑ Status of each port's operation is displayed on the PERMA PRO's LED screen
- ❑ Each port operates independently which ensures continual lubrication even if one port experiences a problem
- ❑ MP6 features an independent motor drive that is powered by the PRO eliminating the need for an outside power source



PRO 250 MP61

**Exclusive
to Applied**

perma®



APPLIED
Industrial Technologies®

PERMA[®] PRO Lubrication System

Battery Powered and/or Remote Locations	
Single Point Lubricators	
Product	Part Number
PRO 250cc	PRO250XX
PRO 500cc	PRO500XX

Multi-Point Lubricators with Installation Kit	
Product	Part Number
PRO 250cc	PRO250MP6IXX
PRO 500cc	PRO500MP6IXX

Multi-Point Lubricators with Installation Kit and Enclosure	
Product	Part Number
PRO 250cc	PRO250LTMP6IXX
PRO 500cc	PRO500LTMP6IXX

Replacement Parts	
Product	Part Number
250cc Canister	PROLV250XX
500cc Canister	PROLV500XX
Installation Kit	PROMP6INSTKITXX

PLC and/or Machine Controlled	
Single Point Lubricators	
Product	Part Number
PRO 250cc	PRO250CXX
PRO 500cc	PRO500CXX

Multi-Point Lubricators with Installation Kit	
Product	Part Number
PRO 250cc	PRO250CMP6IXX
PRO 500cc	PRO500CMP6IXX

Replacement Parts	
Product	Part Number
250cc Canister	PROLV250XX
500cc Canister	PROLV500XX
Installation Kit	PROMP6INSTKITXX



XX - Please specify lubrication type with suffix
LI=Lithium
LICO=Lithium Complex
AC=Aluminum Complex
FG=Food Grade
SYN=Synthetic
EM=Electric Motor

**Contact Your Local Applied Service Center
1-877-279-2799**



WARNING: Injury, death, property damage, and/or equipment failure may result from misuse or misapplication of the products featured in this publication. The information in this publication is provided "AS IS," WITHOUT WARRANTY OF THE INFORMATION'S ACCURACY OR THE PRODUCTS' SUITABILITY FOR ANY PARTICULAR USE.



Corporate Headquarters
One Applied Plaza
Cleveland, Ohio 44115
Toll Free Phone: 1-877-279-2799
www.Applied.com